

# SILICONES

## and more

### Silicone foam Open Cell 7

The Silicone Foam Open Cell 7 is a 2-component (Platinum) Poly-Addition casting silicone that cures at room temperature and foams up to 7 times its volume. This silicone can of course also be colored with silicone dye.

This silicone is used for filling seat cushions, for props and decor and for filling flexible objects and bras, etc. Foam plates/foam mats are also made with this silicone. Silicone foam is also suitable for sealing Lithium batteries (application testing is necessary).

- High frothing
- Returns well to intended shape after compression
- High temperature and chemical resistance
- Easy to process
- Uniform/well distributed density over the entire casting.

#### Technical data

- Mixing ratio by weight: A:B = 100:100
- Processing time (pot life) at 25°C: 2 minutes
- Demoulding time at 25°C: 70 minutes
- Viscosity at 20°C: 11,500 mPa S
- Colour: Whitish, colourless
- Hardness: Shore C 5-10 (Shore A 20-30)
- Density at 20°C: 0.162 g/cm<sup>3</sup>
- Opschium factor in volume: 7
- Flame retardant UL94-V0
- OpenCell

Please note: Pot life/demoulding time is highly dependent on temperature! At a higher temperature, the processing time and demoulding time become shorter.

#### Processing

These silicones can easily be mixed by hand or machine. Mix the A and B components carefully and in the indicated ratio (100 parts A and 100 parts B by weight). Process the mixture within the pot life and wait until it has completely hardened before demoulding. You can possibly speed up the curing process by heating the whole thing. Every 10 degrees the time roughly halves. Please note that in this case air bubbles will have less time to escape.

#### Extra information

You can color the silicone intensely with [silicone dye](#).

Please note: This is a silicone addition. These silicones can be poisoned by sulfur, nitrogen, amino compounds and metal salts. If you are not sure whether the products you are using (including gloves, spatulas and cups) contain these ingredients, do a small test first. These substances are found in many latex gloves, some plastilines, lacquers and glues, condensation silicone, 1-component silicone sealant, natural rubbers and 3D printing material (especially stereolithography). If you still want to use this, you will have to put on a protective layer of [polyvinyl alcohol](#). Please note, the faster the silicone hardens, the less the foam effect. The silicone hardens faster at higher temperatures, so the foam effect cannot fully occur. Silicone that is too cold also gives a less good result because the foam formation starts to collapse again.

So preferably process the silicone at room temperature.

#### Shelf life

Provided the silicone is stored in closed packaging, cool and frost-free, the shelf life is at least one year.

#### Safety requirements

If you work frequently with the silicone, it is recommended to wear gloves during processing and to ventilate the area well. For safety instructions, please refer to the safety data sheet.

### Properties

- ✓ Foam factor 7
- ✓ Hardness Shore C 5-10
- ✓ Flame retardant UL94-V0
- ✓ Open cell structure
- ✓ Mixing ratio (Weight) 100:100
- ✓ Working time 2 minutes
- ✓ Curing time 70 minutes
- ✓ Density 0.162 g/cm<sup>3</sup>